


Solida DC 6.0

Core Type
Chipboard

6/A/2

Panel Properties	
Thickness	38,5 mm nominal
Dimensions	600 x 600 mm
Panel Weight	Approx. 11kg
Core Material	Woodcore
Edge Banding	Circumferential
Panel Top Finish Material	Multiple Options Available
Underside	Hot dipped galvanised steel sheet

Understructure	
Pedestal Type	SSP6 M20
C-profile Type	40 x 40 x 2 mm
Pedestal Caps	38 x 38 x 1mm C-PE 4 way



Tate.®

Tate Global GmbH

Zum Stadion 4, 63808 Haibach, Germany

T: +49 (0) 6021 63949-0 E: infoDE@tateglobal.com W: tateglobal.com/de

© 2025 Tate Global GmbH.

Tate Global GmbH reserves the right to amend or add to the product specifications without prior notice as part of our commitment to continuous improvements and the observance of legal changes.

tate-solida-dc-6-datasheet-en-de-v1 6/2025

**PLANET
PASSIONATE**
#planetpassionate

Solida DC 6.0

Core Type
Chipboard

6/A/2

System performance according to EN 12825:2002

Grid Size	600 x 600 mm
Ultimate Load at the Weakest Point	>14 kN
Working Load	6 kN
Safety Factor	2,0
Deflection Class	A
Uniformly Distributed Load	20 kN/m ²
Rolling Load	20,000 at 3kN
System Tested to FFH	1,000 mm

Fire Protection

13501 -1: 2018	Bfl-S1
13501 -2: 2016	REI60r
DIN4102-2: 1977	Fire-retardant load bearing structure

Resistance to Earth EN1081: 2021

HPL	10 ⁸ - 10 ¹¹ Ohm
HPL Dest	10 ⁶ - 10 ⁷ Ohm
Rubber	> 10 ¹⁰ Ohm
Rubber ESD	10 ⁶ - 9 x 10 ⁷ Ohm
PVC	> 10 ¹⁰ Ohm
PVC SD	10 ⁶ bis 10 ⁹ Ohm

* Resistance to earth values are nominal and may vary between manufacturers

Static Electrical Propensity

EN1815: 2016	≤2.0kV
All Finishes Classified	Antistatic