

Grate Air DC

Ventilation panel made of die-cast aluminium

Panel Properties

Dimensions	600 x 600 mm
Thickness	35–44 mm
Weight per panel	approx. 10,2 kg; 23 kg/m ²
Core material	Die-cast aluminium
Open area	56%

Damper

Slide damper	Factory Mounted
Opposed Blade Damper	Site Mounted

Understructure Properties


Pedestal type	SSP
C-profile	40x40x2 mm

Earth Resistance

> 3 x103 Ω

Panel Performance (DIN EN 12825:2002)

Ultimate load at the weakest point	> 13 kN
Working load	> 6 kN



Tate.®

Tate Global GmbH

Zum Stadion 4, 63808 Haibach, Germany

T: +49 (0) 6021 63949-0 E: infoDE@tateglobal.com W: tateglobal.com/de

© 2025 Tate Global GmbH.

Tate Global GmbH reserves the right to amend or add to the product specifications without prior notice as part of our commitment to continuous improvements and the observance of legal changes.


tate-ferra-grate-air-dc-datasheet-en-de-v1 6/2025



#planetpassionate

Grate Air DC

Ventilation panel made of die-cast aluminium



Static Pressure (Pa)	No Damper (L/s)	Opposed Blade Damper (L/s)		Slide Damper (L/s)	
		open	closed	open	closed
5	495	415	80	285	20
10	710	600	87	320	30
15	850	760	105	385	40
20	1015	880	120	485	45
25	1105	960	145	550	50