

Raised Access Floor Pedestal M16-SG3

CLASS 2

- Top plate with perforation diameter of approx. 6.6 and 3.5 mm for clip-on or screw-in stringers/cross bars
- Base plate with perforation diameter of approx. 7.0 mm for anchoring to unfinished floors
- Fix in the threaded bolt with Tate pedestal adhesive
- Bond to unfinished floors with Tate pedestal adhesive



Pedestal	
Pedestal head	<p>Top plate diameter 90 mm embossed Thickness 3 mm</p> <p>Pedestal tube 21,3x2 mm</p> <p>Tapered pedestal tube with thread M16</p> <p>Top plate with tube centrally welded</p>
Pedestal base	<p>Base plate diameter 80 mm embossed Thickness 1.5 mm</p> <p>Threaded bolt M16 (from DN-04/SG3 onwards with lock nut M16)</p> <p>Base plate with threaded bolt centrally welded</p>

Test Results DIN EN 12825:2002

Class	2
Nominal point load	3 kN
Ultimate load	≥ 6 kN
Depending on the respective Tate system	

Designation

DN-00/SG3-M16 SH 22	18–26 mm
DN-01/SG3-M16 SH 30	24–36 mm
DN-02/SG3-M16 SH 40	30–50 mm
DN-03/SG3-M16 SH 60	45–70 mm
DN-04/SG3-M16 SH 80	60–95 mm
DN-05/SG3-M16 SH 110	85–140 mm
DN-06/SG3-M16 SH 150	120–210 mm
DN-07/SG3-M16 SH 190	160–250 mm
Material	Steel, galvanised (transparent/bluish iridescent passivated)

The adjustment ranges mentioned must be observed



Please scan the QR
code or click [here](#) to
go to the current
product page.



Tate®

Tate Global GmbH

Zum Stadion 4, 63808 Haibach, Germany

T: +49 (0) 6021 63949-0 E: infoDE@tateglobal.com W: tateglobal.com/de

© 2025 Tate Global GmbH.

Tate Global GmbH reserves the right to amend or add to the product specifications without prior notice as part of our commitment to continuous improvements and the observance of legal changes.

tate-pedestal-m16-sg3-product-datasheet-en-de-v3 4/2025



#planetpassionate