


# 40B-SW-50

## ELEMENT CLASS 6

The Tate Caso raised access floor system consists of high-quality floor panels with a highly compressed gypsum fibre core and a circumferential edge protection banding. A steel sheet is applied to the underside of the panel, which contributes to increasing the load-bearing capacity. In conjunction with an appropriately sized substructure, this raised floor system achieves the technical values described below.




Panels	
Thickness	approx. 40,5 mm nominal
Weight per panel	24,5 kg
Dimensions	600 mm x 600 mm
Core material	high-density mineral gypsum fibreboard
Building material class	A1/A2
Edge banding	circumferential
Panel face	surface coverings suitable for raised access floors, e.g. homogeneous vinyl, linoleum, HPL, are installed ex works
Panel bottom	Steel sheet

Statics according to EN 12825:2002 & application guideline	
Ultimate load	>20 kN (50x50 mm stamp)
Working load	10 kN (50x50 mm stamp)
Safety factor	2,0
Deflection class	A

Fire protection according to DIN 4102-2: 1977	
Fire-resistance class	F30 up to clear heights of 1210 mm depending on the substructure used

### Substructures

Pedestal dimensions with tube of at least 24 x 2 mm or to suit the required installation height including SSP or SSL head.



Please scan the QR code or click [here](#) to go to the current product page.



**Tate.**

**Tate Global GmbH**  
Zum Stadion 4, 63808 Haibach, Germany  
T: +49 (0) 6021 63949-0 E: [infoDE@tateglobal.com](mailto:infoDE@tateglobal.com) W: [tateglobal.com/de](http://tateglobal.com/de)

© 2025 Tate Global GmbH.  
Tate Global GmbH reserves the right to amend or add to the product specifications without prior notice as part of our commitment to continuous improvements and the observance of legal changes.

tate-caso-40B-SW-datasheet-en-de-v1 6/2025

**PLANET PASSIONATE**  
#planetpassionate